franz mensch

HYGIENE – natürlich von Mensch

OVERSHOE MACHINES fast – comfortable – favourable

-MEODO



Quality products directly from the manufacturer. For over 45 years.

HYGOMAT

The bestseller series HYGOMAT is particularly economical, favourable and has a huge range of suitable disposable overshoes. The overshoe machines are ideal for mobile use because they work without power. With the HYGOMAT you put on your overshoes 4 times faster than manually. A time saving that really pays off.

from page 3





STEPSTAR

If you are looking for an overshoe machine for very high traffic areas, you will be well equipped with a STEPSTAR. The machines work with electricity and pull a special foil over the shoe. In just a few seconds, the film sits like an overshoe on the foot - extremely fast and efficient.

from page 12





ECOSTEP

For low visitor numbers there are the overshoe dispensers of the series ECOSTEP. The dispensers are very lightweight and provide a cost-effective solution for the short-term use of overshoes. Due to their mechanical function without electricity, they can be set up flexibly.

from page 10

Overshoes

HACCP prescribes them and for clean rooms they are required: disposable overshoes. The wearing of overshoes is one of the most important measures against contamination in hygiene-sensitive areas. Often the putting on of overshoes is perceived as annoying and also guickly becomes a balancing act. Overshoe machines make it much easier for your visitors to don the overshoes.

The matching overshoes can be found directly at the machines.





HYGOSTAR

HYGO STAR

Overshoe machines HYGOMAT

HYGONORM

- 4 times faster than putting on manually
- no electrical power needed
- very user friendly, no stooping
- easy and fast handling, very quiet
- with grip for a more comfortable fit
- extremely clean, because over shoe is not contaminated by touching with your hands
- 100% hygienic, no cross-contamination

CLASSIC

- small, mobile and space saving
- capacity up to 110 overshoes

69,5 x 31,5 x 23 cm, approx. 8,5 kg white-grey 88810

PU/piece: 1

HygoBase

Topseller

COMFORT

PU/piece: 1

- very hygienic, because of stainless steel (back and side walls)
- with 2 castors on the backside can be relocated, very flexible
- especially for clean rooms and pharmaceutical companies



PU/piece: 1



Overshoe | PP

- permeable to air
- for dry areas

46 cm

blue 28604H PU/piece: 10 x 100





HYGO STAR

Overshoe STRONG | PP

• with anti-slip CPE structure on the sole

• permeable to air • for dry areas

46 cm

light blue 28606H white 28600H

PU/piece: 10 x 100



HYGO STAR

Overshoe with strong CPE sole | PP

- very grippy sole in smooth and moist soil
- above **air-permeable** nonwoven fabric

• below waterproof, strong and durable CPE sole

44 cm

white-blue 2860H 28607H white-green

PU/piece: 10 x 70







www.franz-mensch.de Only in the online shop: ✓ order history ✓ without minimum quantity surcharge 5



phone: +49 8241 9633-0

verkauf@franz-mensch.de



HYGONORM



PU/piece: 10 x 110



Overshoe with antistatic band (ESD) | PP / CPE

- antistatic due to deducible black contact band
- 2 variants: pures PP (blue, permeable to air) or with CPE coating (white, waterproof)
- notice: band (black) must have skin contact to ground the body

ANTISTATIK | PP

48 cm blue 28602H

PU/piece: 10 x 100









HYGO STAR

Overshoe | PP with CPE full coating

- very slip resistant, particularly for smooth surfaces
- inside nonwoven

outside CPE coated, waterproof

44 cm

white 28504H PU/piece: 10 x 80 $C \in PSA_{2016/425}^{VO (EU)} CAT_{1} C \in MPG_{EWG}^{93/42/}$







HYGONORM

HYGOSTAR

Overshoe VARIABLE | PP


- with rubber band on the sole for a perfect fit
- suitable for all shoe sizes
- PP nonwoven, breathable
- bottom with structure made of CPE

46 cm

blue

28646H

PU/piece: 10 x 100





Overshoe STRONG | PP

- strong quality
- bottom with anti-slip structure made of CPE
- breathable
- for dry areas

46 cm

blue

28616H

PU/piece: 10 x 80



HYGO STAR

Overshoe STRONG VARIABLE | PP

• fit, anti-slip and strong

- with rubber band on the sole for a perfect fit
- bottom with anti-slip structure made of CPE
- breathable PP nonwoven, strong quality






Overshoe ECONOMY | PE

- very favourable price
- one size • waterproof, ideal as protection from dirt
- only for indoor areas and short time use

28509H

46 cm blue





Selection guide for HYGOMAT overshoes

artno.	28509H	2850H 28507H	28606H 28600H	28604H	2860H 28607H	28504H	28602H	28502H	28616H	28646H	28650H 28656H
name	Overshoe ECONOMY	Overshoe	Overshoe with structur	Overshoe	Overshoe with CPE sole	Overshoe with CPE coated	Overshoe with antistatic band	Overshoe with antistatic band	Overshoe STRONG	Overshoe VARIABLE	Overshoe STRONG VARIABLE
	38	1	A	A	J	X	J.S)	1	1	4
anti-slide sole	-	_	**	_	***	***	-	_	**	*	*
descrip- tion	6	6	t####	####		6	THE REAL	6	11111 11111	THE REAL	
uon					waterproof sole	waterproof sole					
use	for indoor areas and short time use	food area, pharma, hospital	for indoor areas	for indoor areas	for smooth surfaces	for smooth surfaces	protection against static electricity in the industry, only for indoor areas	protection against static electricity in the industry, only for indoor areas	for indoor areas	for indoor areas	for indoor areas



phone: +49 8241 9633-0



HYGONORM

HYGO STAR

Overshoe machine HYGOSTEP

• overshoe is put on within 4 seconds

- for a high amount of visitors
- much faster than manually putting on
- comfortable, due to the holding handle
- suitable, very favourable overshoes made of PE or PP
- hygienic because overshoes are not touched by hands
- electric, for a steady location
- capacity up to 200 overshoes

57 x 29 x 38 cm, 9 kg

white

88814







HYGOSTAR

Overshoe for HYGOSTEP | PE

waterproof

50 cm blue

285095

PU/piece: 21 x 200





Overshoe for HYGOSTEP | PP

- breathable, high wearing comfort
- 46 cm blue


286265

PU/piece: 21 x 90



9





Overshoe for ECOSTEP / ECOSTEP COMFORT

- HDPE: water and abrasion resistant, stable, approx. 10 micron
- LDPE: waterproof, elastic, tearproof, approx. 15 micron
- PP nonwoven: very favourable, breathable, comfortable to wear

for ECOSTEP COMFORT

HDPE

LDPE

blue

50 cm, approx. 10 micron 286091E blue

PU/piece: 10 x 200

PU/piece: 10 x 200



n			

for ECOSTEP

52 cm, approx. 10 micron

46 cm, approx. 15 micron

286090E

285090E

CAT 1

HDPE

blue

blue

LDPE

48 cm, approx. 15 micron

PU/	piece:	10	х	160

C € PSA ^{VO (EU)} _{2016/425}	CAT 1	Ó	HHHA.
---	----------	---	-------

28604E

285091E



PU/piece: 10 x 160	





28604E



PU/piece: 10 x 100

PU/piece: 10 x 100



HYGONORM

HYGOSTAR

Overshoe dispenser ECOSTEP COMFORT

- very favourable solution for short-term use
- works mechanically, without electricity
- comfortable grip for holding
- with window for easy control of rest capacity
- capacity up to 100 overshoes

102 x 30 x 70 cm, 5 kg 88817

silver

PU/piece: 1



HYGOSTAR

Overshoe dispenser ECOSTEP

- very favourable solution for short-term use
- works mechanically, without electricity
- ideal to take away
- capacity up to 50 overshoes

56 x 26 x 22 cm, 3 kg silver

88818

PU/piece: 1









Exclusively at Franz Mensch





HYGOSTAR

Overshoe machine STEPSTAR

- freehand use, for a high amount of visitors
- very fast: PVC foil covers the shoe in only 4 seconds
- suitable for each kind and size of shoe (also high heels)

80 x 44,5 x 33 cm, 21 kg

black-silver 88815





PU/piece: 1

HYGO STAR

Shrink foil for STEPSTAR | PVC

• foil roll to refill for around 1,000 shoes

approx. 28 micron, length: 390 m transparent 44707

PU/roll: 4

NATURE Star Compostable shrink foil for STEPSTAR | PU

• 100% biodegradable and compostable

- patented organic foil for overshoe machine STEPSTAR
- very grippy and ideal for smooth, slippery floors
- suitable for each kind and size of shoe, also socks and high heels
- to be used for STEPSTAR with teflon mat art. 447098 (please order separately)
- approx. 1,000 tear-offs

approx. 40 micron, length 280 m NEW

44709 blue

PU/roll: 4



HYGO STAR

Teflon mat for STEPSTAR

- obligatory for using the compostable shrink foil (art. 44709)
- enables a tidy wraping around of the foot
- just stick on the tread of the STEPSTAR

34 x 12,5 cm NEW

black 447098 PU/piece: 1

NEW: Grippy organic foil

You only get that at Franz Mensch: The first shrink foil for overshoe machines which is **biodegradable**. Decide consciously for this organic foil and act sustainably.

Important: The step matt made of teflon ensures the tidy operation with the organic foil. Please order the teflon mat separately.

> 1. Stick on the black teflon mat

2. Insert the organic foil roll

3. Ready to use!

verkauf@franz-mensch.de



HYGO STAR

HYGONORM



Three times good:

- 1. The foil ensures a safe walking on smooth and slippery floors due to its grippy surface.
- 2. The foil is 100% compostable and the sustainable alternative when it comes to overshoes.
- 3. In combination with the STEPSTAR machine you get a powerful and very clean hygiene system which is easy to handle for you and your visitors.



Selection guide for overshoe machines

				T	OPSELLE	R			
Art. no.	88812	88818	88817	88810	88811	88813	88814	88815	88816
	EASY BOX	ECOSTEP	ECOSTEP COMFORT	HYGOMAT CLASSIC	HYGOMAT COMFORT	HYGOMAT CLEANROOM	HYGOSTEP	STEPSTAR	STEPSTAR COMFORT
overshoe machines				Į		1		Ø	
			Overshoe is pul	lled over road c	or working shoe	2		coats the sh	oe with film
functioning									
economy	extremly favourable	favourable	favourable	great sele	favourable price ection of very hi overshoes	e, igh quality	little higher purchase price, but very favourable overshoes	very favour	ourchase pric ery quickly, able film for lling
capacity (in overshoes/ film breaks)	40	50	100	110	220	220	200	1,000	1,800
use, measu- red by the number of visitors	can be placed anywhere	can be placed anywhere	can be placed anywhere	can be placed anywhere	entry-level for professional use, can be placed mobile anywhere	especially for clean rooms, can be placed anywhere	for fixed location	professional c loca	device for fixed
handling and comfort	refilling requires effort	without holding on, low stability, because very light	with hand- grip low stability, because very light	without holding on, very fast refilling	easy refill comfortab	ing, with a le handgrip	extreme easy refilling with a comfortable handgrip	without holding on	with a comfortab handgrip
speed	slowly putting on	fast put	tting on	very fast, even for Inexperienced		experienced vis	sitors		







HYGO STAR

Overshoe machine STEPSTAR COMFORT

- professional machine for a high amount of visitors
- PVC foil covers the shoe in only 4 seconds
- suitable for each kind and size of shoe (also high heels)
- you save storage costs for overshoes
- electric, for a steady location
- · ideal for the food processing industry, productions, industry, laboratories, medical areas
- very stable, tearproof foil for about 1800 shoes suitable for dry and not too smooth floors

77,8 x 44,5 x 38,2 cm, 18 kg

silver 88816

(()

HYGO STAR

Shrink foil for STEPSTAR COMFORT | PVC

• foil roll to refill for around 1,800 shoes

approx. 28 micron, length: 590 m transparent 44708

PU/roll: 2

PU/piece: 1

HYGOSTAR

Overshoe dispenser EASY BOX

- particularly cost-efficient overshoe dispenser
- for small visitor groups
- capacity for 40 overshoes
- very space saving
- flexible use, without electricity

43,5 x 22,8 x 14,2 cm, 2,2 kg

88812 grey

PU/piece: 1



Overshoe for EASY BOX | PE

50 cm	
blue	28509K

PU/piece: 10 x 100

HYGO STAR

HYGONORM

Franz mensch

Quality products directly from the manufacturer. For over 45 years.





online-shop www.franz-mensch.de



ready for dispatch



free sample service



pallet prices



discount range

New online shop – www.franz-mensch.de



The fastest way for your order. Register now and discover online benefits!

- without minimum quantity surcharge
- ✓ shipment tracking
- all prices at a glance

Franz Mensch GmbH • Werner-von-Siemens-Str. 2 • 86807 Buchloe, Germany phone: +49 8241 9633-0 • fax: +49 8241 9633-100 • e-mail: verkauf@franz-mensch.de

www.franz-mensch.de

Changes and errors excepted. The general terms of business apply. You find them on www.franz-mensch.de/en/terms-and-conditions.